

Pall Ultipleat® SRT Filtration Products

High Pressure Series



UH219

UH319

UH209

Return Line Series



UR619

UR319

UR209

In-Tank Series



UT319

UT279

Multi-element Series



UFV Series

Ultipleat SRT Filter Housings

Series	Flows to	Pressures to†	Length*
High Pressure	UH209	110 lpm (30 USgpm)	350 bar (5,075 psi) 3, 7
	UH219 ¹	230 lpm (60 USgpm)	420 bar (6,100 psi) 4, 8, 13, 20
	UH239	350 lpm (90 USgpm)	420 bar (6,100 psi) 13, 20
	UH319 ¹	600 lpm (160 USgpm)	420 bar (6,100 psi) 8, 13, 20, 40
	UP319	600 lpm (160 USgpm)	250 bar (3,625 psi) 8, 13, 20, 40
Return Line	UR209	120 lpm (32 USgpm)	41 bar (600 psi) 3, 7
	UR219	265 lpm (70 USgpm)	41 bar (600 psi) 4, 8, 13, 20
	UR319	760 lpm (200 USgpm)	41 bar (600 psi) 8, 13, 20, 40
	UR329	600 lpm (160 USgpm)	28 bar (400 psi) 20, 40
	UR619	835 lpm (220 USgpm)	28 bar (400 psi) 20, 40
	UR629	1,050 lpm (280 USgpm)	28 bar (400 psi) 20, 40
	UR649	1,500 lpm (400 USgpm)	28 bar (400 psi) 20, 40
In Tank	UR699	835 lpm (220 USgpm)	28 bar (400 psi) 20, 40
	UT279	265 lpm (70 USgpm)	10 bar (150 psi) 4, 8, 13, 20
	UT319	760 lpm (200 USgpm)	10 bar (150 psi) 8, 13, 20, 40

SRT Multi-element Filter Housings (simplex & duplex)

Series	Flows to	Pressures to†	Length*
UFV03	1,500 lpm (400 USgpm)	10 bar (150 psi)	40
UFV05	2,500 lpm (660 USgpm)	10 bar (150 psi)	40
UFV10	4,500 lpm (1,200 USgpm)	10 bar (150 psi)	40


† see datasheets for fatigue pressure ratings

* nominal lengths available (inches)

¹ manifold mount port option also available

Pall Ultipleat® SRT Filtration Products

Ultipleat SRT Filter Element



Ultipleat SRT Filter Elements

Filter element burst pressure 10 bard (150 psid)

Series	Flows to	Length*
UE209	130 lpm (34 USgpm)	3, 7
UE219 / UE299	285 lpm (75 USgpm)	4, 8, 13, 20
UE319	760 lpm (200 USgpm)	8, 13, 20, 40
UE619	1,135 lpm (300 USgpm)	20, 40

* nominal lengths available (inches)

SRT Dirt-Fuse Filter Elements

For use in SRT Dirt-fuse filters with no by-pass valve.
Filter element burst pressure 210 bard (3,045 psid)

Series	Flows to	Length*
UE201	125 lpm (33 USgpm)	3, 7
UE211	300 lpm (80 USgpm)	13, 20
UE311	760 lpm (200 USgpm)	10, 20, 40

* nominal lengths available (inches)