



Pall VRF Varnish Remediation System

When varnish forms in combustion turbine lubrication and control systems, the effects can be devastating. Significant varnish build-up leads to:

- Sluggish control and/or equipment reliability issues
- Unscheduled maintenance operations/excessive parts replacement
- Problematic start-ups and/or shut-downs
- Forced equipment outages and lost production time

As the leader in gas turbine lubrication and hydraulic fluid control, Pall introduces a very efficient, simple, and proven varnish removal system. Pall VRF (Varnish Removal Filter) will dramatically reduce the varnish potential of the fluid, ensuring long, healthy operation, and control of gas turbines.

Performance

Field experience with Pall VRF on gas turbines showed a rapid and stable reduction in varnish potential rating (VPRSM)¹ well below the recommended levels. Pall VRF will maintain low varnish potential as the entire system gets cleaned up over time, literally pulling varnish off surfaces for removal. A turbine can be rid of varnish issues in a matter of a few weeks. The combination of Pall SRT filter technology to control varnish formation and the Pall VRF to remove existing varnish will ensure elimination of varnish-related problems.

Features

- Conforms to the ANSI B31.1 - Power Piping Code and the ANSI B31.3 - Process Piping Code
- Varnish removal vessel with specially designed adsorptive media, optimized for removal of varnish-forming precursors from the oil
- Outlet filtration with Pall Ultipleat[®] SRT technology, antistatic and rated at $\beta_{12}(c) > 1000$ for additional protection and cleanliness
- Control system designed to maintain optimum oil temperature for the most efficient removal of varnish
- Simple, reliable operation requiring minimal operator attention

Benefits

- Simple, automated, and proven long-term efficiency
- Applicable to all turbine reservoir sizes



Pall VRF equipped with standard cooler option.

- Faster system clean-up, usually within a few weeks
- Low energy consumption

Applications

- Combustion turbine lubricating and control systems
- Steam turbine lubricating and control systems
- Industrial hydraulic fluids

Dimensions

Width: 40" (1,016.0 mm)
Length: 76" (1,930.4 mm)
Height: 66" (1,676.4 mm)
Weight: Approx. 1,570 lb. (712.2 kg)

Design Characteristics

Flow Rate: 11 gpm (41.6 lpm) @ 60Hz
Maximum Inlet Viscosity: 500 SUS (100 cSt)
Inlet Pressure Range: -14" Hg (-0.47 Barg) to 10 psig (0.69 Barg)
Maximum design temperature: 160°F (71°C)
Standard electrical: 480V, 3 phase, 60 Hz; FLA = 8.0 amps
Cooler motor power: 2 HP
Pump motor power: 1.5 HP
Connection size: Inlet - 1.0 NPT, Discharge - 0.75 NPT
Piping: Stainless Steel Tubing - no flexible hoses

¹ VPRSM is a registered service mark of Analysts Incorporated.

Materials of Construction

Materials of construction and paint are compatible with mineral-based fluids and include carbon steel, stainless steel, copper, brass, aluminum, bronze, and fluorocarbon seals. Consult factory for synthetic fluids.

Ordering information

VRF11-■-●-▲-◆-▼

■	Voltage options
W	480/3P/60Hz
1	575/3P/60Hz
R	380/3P/50Hz
T	415/3P/50Hz

●	Mechanical design
0	non coded
XX	Special: ASME/ANSI, PED, CRN, etc. Please consult factory.

▲	Cooler options
N	None
S	Standard air-over-oil cooler
HC	High-capacity water-over-oil cooler

◆	Mobility options
N	None
C	Casters
P	Tow package (rubber tires)

▼	Electrical design options
N	Standard = non-hazardous/non-explosion proof
ZZ	Special: NEC, IEC, CSA, ATEX, etc. Please consult factory.

Spare Parts	Pall Part Number
Varnish removal cartridges	VRF-PGG
Polishing filter element	UE219AS08Z
VRF vessel sealing gasket	55856
Spare o-rings (62mm x 4mm VITON 70 DURO) (used for cartridges, sealing lid, and center post)	54789



Pall Corporation

USA

25 Harbor Park Drive
Port Washington, NY 11050
800.289.7255 toll free
516.484.3600 Phone
516.484.0364 Fax

Canada

Pall Canada Ltd.
7205 Millcreek Drive
Mississauga
Ontario, L5N 3R3
905.542.0330 Phone
905.542.0331 Fax

China

Pall Filter (Beijing) Co., Ltd.
No. 12 Hongda Nanlu
Beijing Economic-Technological
Development Area (BDA)
Beijing 100176, P.R.China
86 10 6780 2288 Phone
86 10 6780 2329 Fax

France

Pall Filtration Industrielle
3, rue des Gaudines
Boite Postale 90234
78102 St-Germain-en-Laye
Cedex
33 1 30 61 38 00 Phone
33 1 30 61 57 08 Fax

Germany

Pall GmbH
Philipp-Reis Strasse 6
D-63303 Dreieich, Germany
49 6103 3070 Phone
49 6103 34037 Fax

Japan

Gotanda Nomura Shoken Building
1-5-1 Nishi Gotanda
Shinagawa-ku, Tokyo 141
81 3 3495 8300 Phone
81 3 3495 5897 Fax

Korea

Il-dong Bldg. 4F. 968-5
Daechi-3Dong,
Gangnamgu, Seoul, 135-736, Korea
82 2 560 7800 Phone
82 2 569 9092 Fax

Russia & former CIS

Pall GmbH
Moscow Representative Office
Vyatskaya Street 27
Building 13-14
127015 Moscow, Russia
7 495 787 7614 Phone
7 495 787 7615 Fax

United Kingdom

Europa House, Havant Street
Portsmouth PO1 3PD
Hampshire, England
44 23 9 230 3303 Phone
44 23 9 230 2509 Fax

Visit us on the Web at www.pall.com, or email us at varnish@pall.com

Pall Corporation has offices and plants throughout the world. For Pall representatives in your area, please go to www.pall.com/contact.

© Copyright 2009, Pall Corporation. Pall, , and Ultipleat are trademarks of Pall Corporation. Filtration. Separation. Solution.SM is a service mark of Pall Corporation.

PGVFDSEnb

Filtration. Separation. Solution.SM