

Profile® M and N Filter Cartridges

The Profile M and N range of filter cartridges are the latest addition to the Profile family of products and have been designed specifically to meet the needs of the automotive paint industry, in particular, the exacting requirements of mica and metallic automotive paint filtration both solvent based and waterborne.

Filtration with no Color Shift

The structure of the filter medium has been designed particularly for fluid classification, that is, it will leave particles of a certain size and smaller unaffected while ensuring the removal of larger particles. Therefore, with appropriate filter selection, the essential solids in the paint, the pigments, aluminium and mica particles can pass through the filter while agglomerates and contaminants will be removed.

Consistent Reliable Performance

The Profile M and N range of filters are manufactured from effectively continuous fibers that are intertwined and bonded together during the spinning process. As a result, there is no media migration or unloading of contaminants from the filter medium as determined by standard tests. The filtrate quality is consistent and re-work due to paint defects can be significantly reduced.

Low Extractables

The filter is constructed entirely from polypropylene and has a wide chemical compatibility. In addition, no silicone, surfactants, regrind or binders are used during the production process. The Profile M and N filter cartridges can therefore withstand the current operating conditions and there is a negligible level of extractables and no detectable silicone.

Quality

Profile M and N filter cartridges are manufactured to a very high standard of quality assurance and cleanliness and in accordance with BS EN ISO 9001:2008. It is the ideal disposable filter option for metallic/mica paints.



Profile M and N Filter Cartridges

Operating Characteristics

Maximum operating differential pressures and temperatures in compatible liquids

Maximum Differential Pressure (ΔP)	Operating Temperature
4.0 bar (58 psid)	up to 30 °C (86 °F)
3.4 bar (49 psid)	up to 50 °C (122 °F)

In fully compatible liquids which do not soften, swell or attack the filter.

Liquid Flow Rate versus Differential Pressure

Flow Rate	Differential Pressure
5 -10 l/min (1.3 - 2.64 US gpm)	0.2 - 0.4 bar (2.9 - 5.8 psi)

Optimum flow for 254 mm (10") nominal length cartridge and solvent based and waterborne paints.

It is advisable to change the filter element when differential pressure reaches 1.5 - 2 bar (21 - 29 psi)

Ordering information

This is a guide to the part numbering structure only, for availability of specific options, please contact Pall.

AB 1 Y 2 18 J

R 1 F Y 2

RM 1 F Y 2

Table 1: Nominal Cartridge Length

Code	Description
1	254 mm (10")
2	508 mm (20")
3	762 mm (30")
4	1016 mm (40")

Table 2: Media Option

Code	Description
M	Coarse grade media for use in metallic/mica paint applications
N	Coarse grade media for use in metallic/mica paint applications



Pall Corporation

Pall Industrial

25 Harbor Park Drive
Port Washington, NY 11050
+1 516 484 3600 telephone
+1 800 289 7255 toll free US

Portsmouth - UK
+44 (0)23 9230 3303 telephone
+44 (0)23 9230 2507 fax
industrialeu@pall.com



**ENABLING A
GREENER
FUTURESM**

Visit us on the Web at www.pall.com

Pall Corporation has offices and plants throughout the world. For Pall representatives in your area, please go to www.pall.com/contact

Because of technological developments related to the products, systems, and/or services described here in, the data and procedures are subject to change without notice. Please consult your Pall representative or visit www.pall.com to verify that this information remains valid.

© Copyright 2011, Pall Corporation. Pall,  and Profile are trademarks of Pall Corporation. ® indicates a trademark registered in the USA. ENABLING A GREENER FUTURE and *Filtration. Separation. Solution.SM* are service marks of Pall Corporation.