

Gaskleen[®]™ Filter Assembly 1 ½ " W-Seal (1.5 nm)



Data Sheet MEGTMW2ENb

Description

Pall's Gaskleen Top Mount (TM) filter assemblies are designed for ≥ 1.5 nanometer filtration of semiconductor process gases. The top mount filter is well-suited for integrated gas delivery systems, providing easy access and change.

Features & Benefits

- Electropolished 316L stainless steel housing
- State-of-the-art 316L stainless steel filter medium
- High temperature and pressure capabilities
- Excellent gas displacement and desorption characteristics
- 100% helium leak tested
- Manufactured and packaged in a cleanroom environment
- Available with a ¼" VCR¹ port on top of assembly for a pressure gauge or other component
- Improved corrosion resistance using Pall's proprietary process



Specifications


Filter Medium	316L stainless steel
Internal Surface Finish	$\leq 0.7 \mu\text{m } R_{\text{max}}$
Housing	Electropolished 316L stainless steel Housing material meets or exceeds VIM / VAR specifications
Removal Rating	$\geq 1.5 \text{ nm}$
Particle Removal Characteristics	10^9 reduction at rated flow of 5 slpm
	10^6 reduction at rated flow of 15 slpm
	10^4 reduction at rated flow of 30 slpm
Connections	W-seal, 1½" interface

Leak Rating	100% helium leak tested to $10^{-9} \text{ atm}\cdot\text{cm}^3/\text{s}$
	Design validated to $10^{-11} \text{ atm}\cdot\text{cm}^3/\text{s}$
Maximum Operating Pressure	0.97 MPa @ 40 °C / 140 psig @ 104 °F
Maximum Allowable Differential Pressure	0.69 MPa @ 40 °C / 100 psid @ 104 °F


¹ VCR is a registered trademark of Swagelok Company

Pressure Drop vs. Gas Flow Rate

F3200




Dimensions




Top view

GTM-3200F4A



Side view



Side view

GTMF3200F4A-VM4

Part Numbers / Ordering Information

Part Number	Description ²	Height (H) (mm / in)	Design Flow Rate (slpm)
GTMF3200F4A	All 316L stainless steel	42 / 1.65	0-30
GTMF3200F4A-VM4	All 316L stainless steel 1/4" VCR port	60 / 2.36	0-30

² Please contact Pall Microelectronics for other configurations.



Microelectronics

25 Harbor Park Drive
Port Washington, NY 11050
+1 516 484 3600 telephone
+1 800 360 7255 toll free US

Nihon Pall Ltd.

6-5-1, Nishishinjuku,
Shinjuku-ku
Tokyo 163-1325 Japan
+81 3 6901 5700 telephone
+81 3 5322 2109 fax

Pall Corporation has offices and plants throughout the world. To locate the Pall office or distributor nearest you, visit www.pall.com/contact.

The information provided in this literature was reviewed for accuracy at the time of publication. Product data may be subject to change without notice. For current information consult your local Pall distributor or contact Pall directly.

IF APPLICABLE Please contact Pall Corporation to verify that the product conforms to your national legislation and/or regional regulatory requirements for water and food contact use.

© Copyright 2025, Pall Corporation. Pall, , and Gaskleen are trademarks of Pall Corporation.® Indicates a trademark registered in the USA.