

# PFA Gaskleen® 6101 Series Filter Assembly (1.5 nm)



Data Sheet MEPGK61ENa

## Description

The PFA-Gaskleen® 6101 Series Filter Assembly is specifically designed for  $\geq 1.5$  nanometer ( $0.0015 \mu\text{m}$ ) filtration of oxygen and specialty gases.

## Features & Benefits

- 316L stainless steel electropolished housing
- All fluoropolymer element
- Wide range of chemical compatibility
- High temperature and pressure capabilities
- Available in both standard and shortened version
- Wide variety of fitting options available
- Compact size (2.2" / 56 mm dia.) for ease of installation
- 100% integrity tested
- Cleanroom manufactured and packaged
- 100% helium leak tested



## Specifications


Filter Medium	PTFE
Core and End Caps	PFA 440HP
O-ring	FEP encapsulated fluoroelastomer
Internal Surface Finish	$\leq 25 \mu\text{in}$ / $0.64 \mu\text{m R}_a$
Housing	Electropolished 316L stainless steel
Removal Rating	$\geq 1.5 \text{ nm}$
Filter Area	$< 232 \text{ cm}^2$ / $0.25 \text{ ft}^2$
Connections	1/4" Gasket Seal, Male (VCR <sup>1</sup> or compatible)
	1/4" Compression Seal (Swagelok <sup>1</sup> or compatible)
	3/8" Gasket Seal, Male (VCR or compatible)
	3/8" Compression Seal (Swagelok or compatible)

Leak Rating	100% helium leak tested to $10^{-7} \text{ atm}\cdot\text{cm}^3/\text{s}$
	Design validated to $10^{-9} \text{ atm}\cdot\text{cm}^3/\text{s}$
Maximum Operating Pressure	5200 kPa @ 121 °C / 750 psig @ 250 °F
Maximum Forward Differential Pressure	700 kPa @ 21 °C / 100 psid @ 70 °F
Maximum Reverse Differential Pressure	340 kPa @ 21 °C / 50 psid @ 70 °F
Packaging	Double bagged
	Outer bag: aluminized mylar
	Inner bag: polyethylene
	N <sub>2</sub> purged
EU Pressure Equipment Directive	Assemblies have been evaluated and designed using SEP per the European Union's Pressure Equipment Directive 2014/68/EU and are not CE marked.


<sup>1</sup> VCR and Swagelok are trademarks of Swagelok Co.

## Pressure Drop vs. Gas Flow Rate


Connection Size: 1/4"



Connection Size: 3/8"



## Dimensions



## Part Numbers / Ordering Information

Part Number	Description	Length (L) (in / mm)
GLFPF6101VM4	PFA Gaskleen : 1/4" Gasket Seal (VCR or Compatible) Male / Male	5.56 / 141
GLFPF6101SM4S	PFA Gaskleen : 1/4" Compression Seal (Swagelok or Compatible) Male / Male	5.56 / 141
GLFPF6101SM6S	PFA Gaskleen : 3/8" Compression Seal (Swagelok or Compatible) Male / Male	5.81 / 148
GLFPF6101VM6 / 8	PFA Gaskleen : 3/8" or 1/2" Gasket Seal (VCR or Compatible) Male / Male	5.81 / 148
SGLFPF6101VM4	Short PFA Gaskleen : 1/4" Gasket Seal (VCR or Compatible) Male / Male	4.94 / 125
SGLFPF6101VM6 / 8M	Short PFA Gaskleen : 3/8" or 1/2" Gasket Seal (VCR or Compatible) Male / Male	5.00 / 127
SGLFPF6101SM4S	Short PFA Gaskleen : 1/4" Compression Seal (Swagelok or Compatible) Male / Male	4.19 / 106

Unit conversion: 1 bar = 100 kilopascals



### Microelectronics

25 Harbor Park Drive  
Port Washington, NY 11050  
+1 516 484 3600 telephone  
+1 800 360 7255 toll free US

### Nihon Pall Ltd.

6-5-1, Nishishinjuku,  
Shinjuku-ku  
Tokyo 163-1325 Japan  
+81 3 6901 5700 telephone  
+81 3 5322 2109 fax

Pall Corporation has offices and plants throughout the world. To locate the Pall office or distributor nearest you, visit [www.pall.com/contact](http://www.pall.com/contact).

The information provided in this literature was reviewed for accuracy at the time of publication. Product data may be subject to change without notice. For current information consult your local Pall distributor or contact Pall directly.

IF APPLICABLE Please contact Pall Corporation to verify that the product conforms to your national legislation and/or regional regulatory requirements for water and food contact use.

© Copyright 2025, Pall Corporation. Pall, , and Gaskleen are trademarks of Pall Corporation.® Indicates a trademark registered in the USA.